


Zurn Wilkins Connected Backflow Preventer

375W1, 375AW1, 375ASTW1,
and W1 Retrofit Kit Order Form



375ASTW1
Connected Backflow Preventer
with Wireless Monitor

Zurn Gateway

Get real-time alerts before there's a real problem.

Connected Backflow Preventers

- Set up alert parameters for warning notifications and severe alerts based on your facility's relief valve discharge capacity
- Customize email and/or text alerts for relief valve discharge events
- Grant access to status, alerts and historic data trends to your staff and third-party service providers
- View your Zurn connected plumbing products status, alerts and historic data trends 24/7 on our secure portal, plumbSMART™

Zurn Gateway

- The Zurn Gateway connects all of your Zurn Connected Products securely to the Zurn Cloud via to the internet so your products can talk to you through plumbSMART
- Supports a virtually unlimited number of Zurn Connected Products within its range (typically 1000-ft radius)
- 2 internet connection options: Wired (Ethernet) or wireless (LTE Cellular)
- Simple plug-and-play installation
- Securely transmits encrypted data between Zurn Connected Products and Zurn Cloud
- Designed to protect local area network (LAN) from unauthorized access through device

Retrofit Kits Available

Already have a Zurn Wilkins Reduced Pressure Backflow Preventer installed? Simply upgrade your existing valve to a Connected Backflow Preventer with our Retrofit Kit.

| Size | 2-1/2" - 6" (212-6-RFK-375W1) | 8" - 10" (8-10-RFK-375W1) |
|------|-------------------------------|---------------------------|
| | | |



Learn more at zurn.com/plumbsmart

Zurn Wilkins Connected Backflow Preventer Order Form

| | |
|---------------------|---------------------|
| Contractor Firm | Contractor Contact |
| Contractor Address | Contractor Cell # |
| Contractor City | Contractor Email |
| Contractor State | Rep Agency |
| Contractor Zip Code | Rep Contact |
| Project Location | Distributor |
| Deliver by Date | Distributor Contact |

ORDER INFORMATION

| Size | 2-1/2" | 3" | 4" | 6" | 8" | 10" |
|------|--------|----|----|----|----|-----|
|------|--------|----|----|----|----|-----|

| 375W1 | 375AW1 | 375ASTW1 | RETROFIT KIT |
|---|---|--|--------------|
| Ductile Iron Flanged Body, Standard Valve (Lead Free) | Ductile Iron Grooved Body, Standard Valve (Lead Free) | Stainless Steel Grooved Body, Standard Valve (Lead Free) | |

| BACKFLOW | |
|------------------------------------|----------------------------|
| SHUT-OFF VALVES (CHECK ONE) | |
| | NRS Gate Valves (standard) |
| OSY | OS&Y Gate Valves |
| B | Butterfly Gate Valves |

| END CONNECTIONS (CHECK ONE) | |
|-----------------------------|---|
| | Flange x Flange User Connections (standard) |
| FG | Flange x Groove User Connections |
| G | Groove x Groove User Connections |
| GF | Groove x Flange User Connections |

| REPLACEMENTS | |
|--------------|---|
| R | Replacement Spool (custom length) <i>(if "R" is needed additional 300AR Series Backflow Preventer Order Form must be completed along with this form)</i> |

| Accessories | | |
|-------------|---|---------------|
| | Wye Strainer on Inlet - only on flanged inlet choices (FSC) | Air gap (-AG) |


| Shipping details |
|---------------------------------|
| Shipping destination for valve: |

| RETROFIT KIT ONLY applies for existing Zurn Wilkins RP Backflow Preventers | | |
|--|-------------------------------|---------------------------|
| Size | 2-1/2" - 6" (212-6-RFK-375W1) | 8" - 10" (8-10-RFK-375W1) |
| Must also complete GATEWAY portion of Order Form | | |

| GATEWAY | | |
|---|--------------------------------|--|
| Is there already a Zurn Gateway (#1 in diagram) installed within 1000 feet of the location this product will be installed? | | |
| Yes, I already have a gateway | No, I need a gateway | I don't want system monitoring at this time. |
| If gateway needed, then please select preferred mode of data transmission: | | |
| Ethernet (ZGW-LORA-W1-ETH) | LTE cellular (ZGW-LORA-W1-LTE) | |

| Contact person at site to verify gateway connectivity selection and/or cellular signal strength: | |
|--|---------|
| Name | Phone # |

| Shipping details |
|--|
| Zurn gateway shipped to same location (<i>ships UPS</i>) |



End-Point Monitor (#2, see diagram) comes with a 6ft power cord, 120vac outlet must be provided nearby.

| FOR ZURN WILKINS CUSTOMER CARE ONLY | | |
|---|------|--------|
| Sales Order # | PO # | Part # |
| Input Tracking Code: Track0000065 Smart Order | | |

Email or fax this Order Form with the Purchase Order to: Zurn Wilkins Customer Care, email: wilkinscs@zurn.com, fax: 805.237.7197.

